



RACING PERFORMANCE MUSCLE RPM BELT DIMENSION CHART



ENGINEERED FOR PERFORMANCE

Gates RPM belts are specifically engineered for forced induction and high-output engines. Featuring a high-modulus, low stretch Aramid or Polyester tensile cord, nylon-fiber reinforced undercord, and dual adhesion gum layers, these belts can handle more power and withstand more punishment than any other belt on the market.

GOT BELT ISSUES? GET GATES RPM.

PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K030250RPM	K03 13/32" x 25 3/4" - Black	3	25.17	639	25.731	654
K030295RPM	K03 13/32" x 30 1/8" - Black	3	29.55	751	30.111	765
K030300RPM	K03 13/32" x 30 3/4" - Black	3	30.19	767	30.755	781
K030334RPM	K03 13/32" x 34" - Black	3	33.46	850	34.024	864
K040220RPM	K04 9/16" x 22 3/4" - Black	4	22.11	562	22.75	578
K040274RPM	K04 9/16" x 28" - Black	4	27.38	695	27.95	710
K040292RPM	K04 9/16" x 29 3/4" - Black	4	29.19	741	29.75	756
K040300RPM	K04 9/16" x 30 3/4" - Black	4	30.17	766	30.74	781
K040305RPM	K04 9/16" x 31 1/4" - Black	4	30.65	779	31.213	792
K040310RPM	K04 9/16" x 31 5/8" - Black	4	31.13	791	31.625	803
K040315RPM	K04 9/16" x 32 1/4" - Black	4	31.65	804	32.25	818
K040322RPM	K04 9/16" x 32 7/8" - Black	4	32.35	822	32.875	835
K040325RPM	K04 9/16" x 33 1/4" - Black	4	32.64	829	33.25	845
K040329RPM	K04 9/16" x 33 3/8" - Black	4	32.87	835	33.375	849
K040330RPM	K04 9/16" x 33 5/8" - Black	4	33.13	842	33.625	854
K040332RPM	K04 9/16" x 33 3/4" - Black	4	33.2	843	33.75	857
K040335RPM	K04 9/16" x 34" - Black	4	33.46	850	34	864
K040338RPM	K04 9/16" x 34 3/8" - Black	4	33.86	860	34.375	874
K040340RPM	K04 9/16" x 34 5/8" - Black	4	34.124	867	34.625	879
K040345RPM	K04 9/16" x 35" - Black	4	34.44	875	35	889
K040347RPM	K04 9/16" x 35 1/4" - Black	4	34.75	883	35.25	895
K040353RPM	K04 9/16" x 35 7/8" - Black	4	35.33	897	35.875	912
K040355RPM	K04 9/16" x 36 1/8" - Black	4	35.56	903	36.125	918
K040360RPM	K04 9/16" x 36 3/4" - Black	4	36.14	918	36.75	933
K040365RPM	K04 9/16" x 37 1/8" - Black	4	36.56	929	37.125	943
K040370RPM	K04 9/16" x 37 1/2" - Black	4	36.994	940	37.5	953
K040372RPM	K04 9/16" x 38" - Black	4	37.38	949	38	964
K040384RPM	K04 9/16" x 39" - Black	4	38.425	976	39	991
K040385RPM	K04 9/16" x 39 1/8" - Black	4	38.52	978	39.09	993
K040390RPM	K04 9/16" x 39 5/8" - Black	4	39.13	994	39.625	1008
K040398RPM	K04 9/16" x 40 3/8" - Black	4	39.87	1013	40.375	1027
K040400RPM	K04 9/16" x 40 5/8" - Black	4	40.133	1019	40.625	1032
K040405RPM	K04 9/16" x 41 1/4" - Black	4	40.649	1032	41.25	1047
K040410RPM	K04 9/16" x 41 5/8" - Black	4	41.126	1045	41.625	1057
K040413RPM	K04 9/16" x 42" - Black	4	41.503	1054	42	1067



PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K040420RPM	K04 9/16" x 42 5/8" - Black	4	42.13	1070	42.625	1084
K040430RPM	K04 9/16" x 43 3/4" - Black	4	43.15	1096	43.75	1111
K040440RPM	K04 9/16" x 44 5/8" - Black	4	44.125	1121	44.625	1133
K040476RPM	K04 9/16" x 48 1/8" - Black	4	47.61	1209	48.13	1223
K040490RPM	K04 9/16" x 49 1/2" - Black	4	48.97	1244	49.537	1258
K040500RPM	K04 9/16" x 50 5/8" - Black	4	50.07	1272	50.625	1286
K040517RPM	K04 9/16" x 52 1/8" - Black	4	51.6	1311	52.125	1325
K040530RPM	K04 9/16" x 53 1/2" - Black	4	53	1346	53.5	1359
K040551RPM	K04 9/16" x 55 3/4" - Black	4	55.13	1400	55.75	1415
K050321RPM	K05 21/32" x 32 3/4" - Black	5	32.16	817	32.75	831
K050336RPM	K05 21/32" x 34 1/4" - Black	5	33.75	857	34.25	871
K050344RPM	K05 21/32" x 35" - Black	5	34.44	875	35	889
K050345RPM	K05 21/32" x 35 1/4" - Black	5	34.64	880	35.25	895
K050350RPM	K05 21/32" x 35 5/8" - Black	5	35.1	891	35.625	905
K050380RPM	K05 21/32" x 38 5/8" - Black	5	38.14	969	38.625	981
K050390RPM	K05 21/32" x 39 5/8" - Black	5	39.13	994	39.625	1006
K050400RPM	K05 21/32" x 40 5/8" - Black	5	40.01	1016	40.625	1032
K050415RPM	K05 21/32" x 42" - Black	5	41.5	1054	42	1068
K050420RPM	K05 21/32" x 42 5/8" - Black	5	42.12	1070	42.625	1083
K050425RPM	K05 21/32" x 43 1/8" - Black	5	42.54	1081	43.125	1094
K050435RPM	K05 21/32" x 44 1/8" - Black	5	43.62	1108	44.125	1121
K050507RPM	K05 21/32" x 51 1/8" - Black	5	50.61	1285	51.125	1299
K050516RPM	K05 21/32" x 52 1/4" - Black	5	51.66	1312	52.225	1327
K050705RPM	K05 21/32" x 71 1/8" - Black	5	70.57	1792	71.135	1807
K050789RPM	K05 21/32" x 79 1/2" - Black	5	78.9	2004	79.5	2019
K050887RPM	K05 21/32" x 89 1/8" - Black	5	88.61	2251	89.173	2265
K060338RPM	K06 13/16" x 34 3/8" - Black	6	33.8	859	34.375	873
K060355RPM	K06 13/16" x 36 1/8" - Black	6	35.56	903	36.125	918
K060370RPM	K06 13/16" x 37 5/8" - Black	6	37.13	943	37.625	957
K060374RPM	K06 13/16" x 37 7/8" - Black	6	37.38	949	37.875	963
K060388RPM	K06 13/16" x 39 3/8" - Black	6	38.78	985	39.375	999
K060448RPM	K06 13/16" x 45 3/8" - Black	6	44.84	1139	45.375	1153
K060465RPM	K06 13/16" x 47" - Black	6	46.48	1181	47	1195
K060478RPM	K06 13/16" x 48 1/4" - Black	6	47.72	1212	48.25	1227
K060480RPM	K06 13/16" x 48 5/8" - Black	6	48.12	1222	48.63	1235
K060490RPM	K06 13/16" x 49 1/2" - Black	6	48.97	1244	49.537	1258
K060525RPM	K06 13/16" x 53 3/8" - Black	6	52.76	1340	53.375	1356
K060532RPM	K06 13/16" x 53 7/8" - Black	6	53.27	1353	53.835	1367
K060535RPM	K06 13/16" x 54 1/4" - Black	6	53.71	1364	54.272	1379
K060539RPM	K06 13/16" x 54 1/2" - Black	6	53.96	1371	54.521	1385
K060547RPM	K06 13/16" x 55 1/4" - Black	6	54.71	1390	55.276	1404
K060551RPM	K06 13/16" x 55 3/4" - Black	6	55.13	1400	55.7	1415
K060555RPM	K06 13/16" x 56" - Black	6	55.46	1409	56.022	1423
K060605RPM	K06 13/16" x 61 1/8" - Black	6	60.59	1539	61.151	1553
K060642RPM	K06 13/16" x 64 3/4" - Black	6	64.24	1632	64.809	1646
K060667RPM	K06 13/16" x 67 1/4" - Black	6	66.69	1694	67.254	1708
K060680RPM	K06 13/16" x 68 5/8" - Black	6	68	1727	68.567	1742
K060685RPM	K06 13/16" x 69 1/8" - Black	6	68.57	1742	69.133	1756



PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K060690RPM	K06 13/16" x 69 5/8" - Black	6	69.01	1753	69.57	1767
K060705RPM	K06 13/16" x 71 1/8" - Black	6	70.57	1792	71.135	1807
K060739RPM	K06 13/16" x 74 1/2" - Black	6	73.97	1879	74.531	1893
K060744RPM	K06 13/16" x 75" - Black	6	74.39	1890	74.955	1904
K060763RPM	K06 13/16" x 76 7/8" - Black	6	76.25	1937	76.817	1951
K060775RPM	K06 13/16" x 78" - Black	6	77.48	1968	78.04	1982
K060785RPM	K06 13/16" x 79" - Black	6	78.47	1993	79	2007
K060798RPM	K06 13/16" x 80 3/8" - Black	6	79.76	2026	80.326	2040
K060804RPM	K06 13/16" x 81" - Black	6	80.45	2043	81	2057
K060806RPM	K06 13/16" x 81 1/8" - Black	6	80.58	2047	81.141	2061
K060810RPM	K06 13/16" x 81 5/8" - Black	6	81.04	2058	81.608	2073
K060815RPM	K06 13/16" x 82 1/8" - Black	6	81.54	2071	82.125	2085
K060825RPM	K06 13/16" x 83 1/8" - Black	6	82.59	2098	83.155	2112
K060827RPM	K06 13/16" x 83 1/4" - Black	6	82.72	2101	83.288	2116
K060832RPM	K06 13/16" x 83 3/4" - Black	6	83.19	2113	83.755	2127
K060837RPM	K06 13/16" x 84 1/4" - Black	6	83.68	2125	84.242	2140
K060845RPM	K06 13/16" x 85 1/4" - Black	6	84.66	2150	85.23	2165
K060854RPM	K06 13/16" x 85 7/8" - Black	6	85.33	2167	85.892	2182
K060868RPM	K06 13/16" x 87 3/8" - Black	6	86.78	2204	87.345	2219
K060878RPM	K06 13/16" x 88 3/8" - Black	6	87.82	2231	88.387	2245
K060882RPM	K06 13/16" x 88 7/8" - Black	6	88.3	2243	88.87	2257
K060888RPM	K06 13/16" x 89 1/2" - Black	6	88.9	2258	89.47	2273
K060891RPM	K06 13/16" x 89 3/4" - Black	6	89.13	2264	89.695	2278
K060895RPM	K06 13/16" x 90 1/8" - Black	6	89.56	2275	90.127	2289
K060896RPM	K06 13/16" x 89 21/32" - Black	6	89.562	2294	89.66	2277
K060900RPM	K06 13/16" x 90 5/8" - Black	6	90.03	2287	90.595	2301
K060905RPM	K06 13/16" x 90 7/8" - Black	6	90.31	2294	90.873	2308
K060908RPM	K06 13/16" x 91 1/4" - Black	6	90.71	2304	91.27	2318
K060910RPM	K06 13/16" x 91 5/8" - Black	6	91.11	2314	91.68	2329
K060915RPM	K06 13/16" x 92 1/8" - Black	6	91.56	2326	92.125	2340
K060926RPM	K06 13/16" x 93 1/8" - Black	6	92.5	2350	93.069	2364
K060935RPM	K06 13/16" x 94" - Black	6	93.42	2373	93.985	2387
K060938RPM	K06 13/16" x 94 1/2" - Black	6	93.9	2385	94.47	2400
K060947RPM	K06 13/16" x 95 1/4" - Black	6	94.67	2405	95.236	2419
K060950RPM	K06 13/16" x 95 5/8" - Black	6	95.02	2414	95.585	2428
K060962RPM	K06 13/16" x 96 7/8" - Black	6	96.29	2446	96.855	2460
K060970RPM	K06 13/16" x 97 5/8" - Black	6	97.02	2464	97.582	2479
K060975RPM	K06 13/16" x 98 1/8" - Black	6	97.54	2478	98.11	2492
K060980RPM	K06 13/16" x 98 5/8" - Black	6	98.07	2491	98.64	2505
K060990RPM	K06 13/16" x 99 5/8" - Black	6	99.08	2517	99.65	2531
K060994RPM	K06 13/16" x 99 7/8" - Black	6	99.3	2522	99.865	2537
K061000RPM	K06 13/16" x 100 5/8" - Black	6	100.01	2540	100.58	2555
K061005RPM	K06 13/16" x 101 1/8" - Black	6	100.54	2554	101.11	2568
K061010RPM	K06 13/16" x 101 5/8" - Black	6	101.06	2567	101.63	2581
K061015RPM	K06 13/16" x 102 1/8" - Black	6	101.52	2579	102.09	2593
K061020RPM	K06 13/16" x 102 5/8" - Black	6	102	2591	102.57	2605
K061025RPM	K06 13/16" x 103" - Black	6	102.4	2601	102.97	2615
K061031RPM	K06 13/16" x 103 5/8" - Black	6	103.1	2619	103.67	2633

PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K061033RPM	K06 13/16" x 103 7/8" - Black	6	103.31	2624	103.88	2639
K061037RPM	K06 13/16" x 104 1/4" - Black	6	103.74	2635	104.31	2649
K061040RPM	K06 13/16" x 104 5/8" - Black	6	104	2642	104.66	2658
K061045RPM	K06 13/16" x 105" - Black	6	104.4	2652	104.97	2666
K061054RPM	K06 13/16" x 106" - Black	6	105.43	2678	106	2692
K061058RPM	K06 13/16" x 106 3/8" - Black	6	105.77	2687	106.34	2701
K061066RPM	K06 13/16" x 107 1/8" - Black	6	106.61	2708	107.175	2722
K061073RPM	K06 13/16" x 107 7/8" - Black	6	107.35	2727	107.92	2741
K061075RPM	K06 13/16" x 108 1/8" - Black	6	107.55	2732	108.115	2746
K061080RPM	K06 13/16" x 108 3/4" - Black	6	108.14	2747	108.71	2761
K061098RPM	K06 13/16" x 109 3/8" - Black	6	108.87	2765	109.44	2780
K061110RPM	K06 13/16" x 111 5/8" - Black	6	111.06	2821	111.63	2835
K061119RPM	K06 13/16" x 112" - Black	6	111.93	2843	111.99	2845
K061120RPM	K06 13/16" x 112 1/2" - Black	6	111.99	2845	112.56	2859
K061123RPM	K06 13/16" x 112 7/8" - Black	6	112.37	2854	112.935	2869
K061130RPM	K06 13/16" x 113 5/8" - Black	6	113.05	2871	113.62	2886
K061140RPM	K06 13/16" x 114 1/2" - Black	6	113.99	2895	114.555	2910
K061145RPM	K06 13/16" x 115 1/4" - Black	6	114.65	2912	115.22	2927
K061187RPM	K06 13/16" x 119 1/4" - Black	6	118.74	3016	119.31	3030
K061247RPM	K06 13/16" x 125 1/4" - Black	6	124.76	3169	125.25	3183
K061251RPM	K06 13/16" x 125 5/8" - Black	6	125.09	3177	125.66	3192
K070500RPM	K07 15/16" x 50 5/8" - Black	7	50.07	1272	50.625	1286
K070653RPM	K07 15/16" x 65 7/8" - Black	7	65.36	1660	65.93	1675
K070680RPM	K07 15/16" x 68 5/8" - Black	7	68.06	1729	68.626	1743
K070730RPM	K07 15/16" x 73 5/8" - Black	7	73.09	1856	73.625	1870
K070745RPM	K07 15/16" x 75 1/4" - Black	7	74.567	1894	75.23	1911
K070763RPM	K07 15/16" x 76 7/8" - Black	7	76.25	1937	76.817	1951
K070795RPM	K07 15/16" x 80" - Black	7	79.5	2019	80	2033
K070810RPM	K07 15/16" x 81 5/8" - Black	7	81.04	2058	81.625	2073
K070825RPM	K07 15/16" x 83 1/8" - Black	7	82.59	2098	83.155	2112
K070852RPM	K07 15/16" x 85 3/4" - Black	7	85.21	2164	85.75	2178
K070896RPM	K07 15/16" x 90 1/8" - Black	7	89.56	2275	90.127	2289
K071065RPM	K07 15/16" x 107 1/8" - Black	7	106.53	2706	107.125	2720
K071141RPM	K07 15/16" x 114 5/8" - Black	7	114.08	2898	114.645	2912
K071150RPM	K07 15/16" x 115 5/8" - Black	7	115.04	2922	115.61	2936
K080220RPM	K08 1 3/32" x 22 3/4" - Black	8	22.107	562	22.77	578
K080408RPM	K08 1 3/32" x 41 3/8" - Black	8	40.79	1036	41.36	1051
K080415RPM	K08 1 3/32" x 42 1/8" - Black	8	41.5	1054	42.068	1069
K080435RPM	K08 1 3/32" x 44 1/8" - Black	8	43.62	1108	44.19	1122
K080450RPM	K08 1 3/32" x 45 5/8" - Black	8	45.12	1146	45.685	1160
K080465RPM	K08 1 3/32" x 47" - Black	8	46.48	1181	47.044	1195
K080468RPM	K08 1 3/32" x 47 3/8" - Black	8	46.82	1189	47.375	1203
K080471RPM	K08 1 3/32" x 47 3/4" - Black	8	47.12	1197	47.69	1211
K080480RPM	K08 1 3/32" x 48 5/8" - Black	8	48.12	1222	48.685	1237
K080485RPM	K08 1 3/32" x 49 1/8" - Black	8	48.59	1234	49.155	1249
K080491RPM	K08 1 3/32" x 49 5/8" - Black	8	49.11	1247	49.625	1260
K080496RPM	K08 1 3/32" x 50 1/8" - Black	8	49.61	1260	50.172	1274



PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K080507RPM	K08 1 3/32" x 51 1/4" - Black	8	50.748	1289	51.25	1302
K080525RPM	K08 1 3/32" x 53 1/8" - Black	8	52.6	1336	53.169	1351
K080530RPM	K08 1 3/32" x 53 1/2" - Black	8	52.95	1345	53.517	1359
K080537RPM	K08 1 3/32" x 54 1/4" - Black	8	53.71	1364	54.272	1379
K080539RPM	K08 1 3/32" x 54 1/2" - Black	8	53.95	1370	54.5	1384
K080545RPM	K08 1 3/32" x 55 1/8" - Black	8	54.5	1384	55.068	1399
K080550RPM	K08 1 3/32" x 55 3/4" - Black	8	55.13	1400	55.694	1415
K080560RPM	K08 1 3/32" x 56 5/8" - Black	8	56.09	1425	56.658	1439
K080600RPM	K08 1 3/32" x 60 5/8" - Black	8	60	1524	60.565	1538
K080605RPM	K08 1 3/32" x 61 1/8" - Black	8	60.59	1539	61.151	1553
K080610RPM	K08 1 3/32" x 61 3/4" - Black	8	61.22	1555	61.787	1569
K080615RPM	K08 1 3/32" x 62 1/8" - Black	8	61.51	1562	62.076	1577
K080630RPM	K08 1 3/32" x 63 5/8" - Black	8	63.04	1601	63.606	1616
K080640RPM	K08 1 3/32" x 64 1/2" - Black	8	64	1626	64.5	1638
K080645RPM	K08 1 3/32" x 65 1/4" - Black	8	64.67	1643	65.237	1657
K080653RPM	K08 1 3/32" x 65 7/8" - Black	8	65.36	1660	65.922	1674
K080655RPM	K08 1 3/32" x 66 1/4" - Black	8	65.7	1669	66.27	1683
K080660RPM	K08 1 3/32" x 66 1/2" - Black	8	65.99	1676	66.559	1691
K080661RPM	K08 1 3/32" x 66 3/4" - Black	8	66.14	1680	66.75	1695
K080670RPM	K08 1 3/32" x 67 1/2" - Black	8	66.98	1701	67.543	1716
K080675RPM	K08 1 3/32" x 68 1/16" - Black	8	67.49	1714	68.05	1728
K080680RPM	K08 1 3/32" x 68 5/8" - Black	8	68	1727	68.567	1742
K080685RPM	K08 1 3/32" x 69 1/8" - Black	8	68.57	1742	69.133	1756
K080690RPM	K08 1 3/32" x 69 5/8" - Black	8	69.01	1753	69.57	1767
K080700RPM	K08 1 3/32" x 70 1/2" - Black	8	69.88	1775	70.445	1789
K080708RPM	K08 1 3/32" x 71 1/4" - Black	8	70.74	1797	71.3	1811
K080716RPM	K08 1 3/32" x 72 1/8" - Black	8	71.53	1817	72.095	1831
K080751RPM	K08 1 3/32" x 75 5/8" - Black	8	75.08	1907	75.63	1921
K080765RPM	K08 1 3/32" x 77" - Black	8	76.48	1943	77.046	1957
K080780RPM	K08 1 3/32" x 78 5/8" - Black	8	78.02	1982	78.586	1996
K080794RPM	K08 1 3/32" x 80" - Black	8	79.45	2018	80	2032
K080797RPM	K08 1 3/32" x 80 1/8" - Black	8	79.62	2022	80.187	2037
K080810RPM	K08 1 3/32" x 82 5/8" - Black	8	81.04	2058	81.608	2073
K080817RPM	K08 1 3/32" x 82 3/8" - Black	8	81.77	2077	82.34	2091
K080828RPM	K08 1 3/32" x 83 3/8" - Black	8	82.87	2105	83.38	2118
K080842RPM	K08 1 3/32" x 84 3/4" - Black	8	84.23	2139	84.799	2154
K080845RPM	K08 1 3/32" x 85 1/8" - Black	8	84.54	2147	85.13	2162
K080850RPM	K08 1 3/32" x 85 3/8" - Black	8	85.08	2161	85.375	2175
K080852RPM	K08 1 3/32" x 85 3/4" - Black	8	85.24	2165	85.75	2178
K080855RPM	K08 1 3/32" x 86 1/8" - Black	8	85.56	2173	86.121	2187
K080865RPM	K08 1 3/32" x 87 1/8" - Black	8	86.53	2198	87.125	2212
K080885RPM	K08 1 3/32" x 89 1/8" - Black	8	88.54	2249	89.105	2263
K080889RPM	K08 1 3/32" x 89 1/2" - Black	8	88.9	2258	89.5	2272
K080893RPM	K08 1 3/32" x 89 7/8" - Black	8	89.28	2268	89.849	2282
K080903RPM	K08 1 3/32" x 90 7/8" - Black	8	90.31	2294	90.873	2308
K080910RPM	K08 1 3/32" x 91 5/8" - Black	8	91.02	2312	91.59	2326
K080915RPM	K08 1 3/32" x 92 1/8" - Black	8	91.52	2325	92.125	2340
K080922RPM	K08 1 3/32" x 92 3/4" - Black	8	92.16	2341	92.721	2355



PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K080956RPM	K08 1 3/32" x 96 1/4" - Black	8	95.67	2430	96.25	2444
K081000RPM	K08 1 3/32" x 100 5/8" - Black	8	100.01	2540	100.58	2555
K081088RPM	K08 1 3/32" x 109 3/8" - Black	8	108.8	2764	109.375	2778
K100234RPM	K10 1 3/8" x 24" - Black	10	23.4	594	24	608
K100475RPM	K10 1 3/8" x 48" - Black	10	47.5	1207	48	1219
K100525RPM	K10 1 3/8" x 53" - Black	10	52.5	1334	53	1346
K100529RPM	K10 1 3/8" x 53 3/8" - Black	10	52.95	1345	53.38	1356
K100535RPM	K10 1 3/8" x 54" - Black	10	53.48	1358	54.044	1373
K100540RPM	K10 1 3/8" x 54 1/2" - Black	10	53.96	1371	54.521	1385
K100563RPM	K10 1 3/8" x 56 7/8" - Black	10	56.29	1430	56.857	1444
K100564RPM	K10 1 3/8" x 57" - Black	10	56.45	1434	57	1448
K100570RPM	K10 1 3/8" x 57 1/2" - Black	10	56.99	1448	57.553	1462
K100572RPM	K10 1 3/8" x 57 7/8" - Black	10	57.25	1454	57.88	1469
K100575RPM	K10 1 3/8" x 58 1/8" - Black	10	57.51	1461	58.07	1475
K100576RPM	K10 1 3/8" x 58 1/4" - Black	10	57.68	1465	58.25	1480
K100579RPM	K10 1 3/8" x 58 1/2" - Black	10	57.96	1472	58.527	1487
K100582RPM	K10 1 3/8" x 58 3/4" - Black	10	58.2	1478	58.75	1492
K100594RPM	K10 1 3/8" x 60" - Black	10	59.4	1509	59.97	1523
K100600RPM	K10 1 3/8" x 60 1/2" - Black	10	60	1524	60.5	1538
K100607RPM	K10 1 3/8" x 61 1/4" - Black	10	60.75	1543	61.31	1557
K100618RPM	K10 1 3/8" x 62 3/8" - Black	10	61.83	1570	62.4	1585
K100637RPM	K10 1 3/8" x 64 1/4" - Black	10	63.74	1619	64.302	1633
K100640RPM	K10 1 3/8" x 64 5/8" - Black	10	64.07	1627	64.63	1642
K100655RPM	K10 1 3/8" x 66" - Black	10	65.5	1664	66.062	1678
K100665RPM	K10 1 3/8" x 67 1/8" - Black	10	66.53	1690	67.095	1704
K100670RPM	K10 1 3/8" x 67 1/2" - Black	10	66.98	1701	67.55	1716
K100702RPM	K10 1 3/8" x 70 7/8" - Black	10	70.27	1785	70.875	1800
K100719RPM	K10 1 3/8" x 72 3/8" - Black	10	71.87	1825	72.433	1840
K100731RPM	K10 1 3/8" x 73 5/8" - Black	10	73.09	1856	73.656	1871
K100772RPM	K10 1 3/8" x 77 3/4" - Black	10	77.2	1961	77.75	1975
K100789RPM	K10 1 3/8" x 79 1/2" - Black	10	78.9	2004	79.47	2019
K100816RPM	K10 1 3/8" x 82 1/8" - Black	10	81.57	2072	82.14	2086
K100837RPM	K10 1 3/8" x 84 1/4" - Black	10	83.66	2125	84.25	2140
K100840RPM	K10 1 3/8" x 84 5/8" - Black	10	84.06	2135	84.625	2149
K100878RPM	K10 1 3/8" x 88 3/8" - Black	10	87.82	2231	88.38	2245
K100891RPM	K10 1 3/8" x 89 3/4" - Black	10	89.13	2264	89.69	2278
K101010RPM	K10 1 3/8" x 101 1/2" - Black	10	101	2565	101.5	2579
K101065RPM	K10 1 3/8" x 107 1/8" - Black	10	106.53	2706	107.125	2720
K101078RPM	K10 1 3/8" x 108 3/8" - Black	10	107.87	2740	108.375	2753
K110815RPM	K11 1 1/2" x 82" - Black	11	81.46	2069	82	2083
K110825RPM	K11 1 1/2" x 83 1/8" - Black	11	82.59	2098	83.13	2111
K110841RPM	K11 1 1/2" x 84 3/4" - Black	11	84.16	2138	84.75	2153
K120559RPM	K12 1 21/32" x 56 1/2" - Black	12	55.95	1421	56.519	1436
K120594RPM	K12 1 21/32" x 60" - Black	12	59.4	1509	59.97	1523
K120606RPM	K12 1 21/32" x 61 1/8" - Black	12	60.59	1539	61.16	1553
K120610RPM	K12 1 21/32" x 61 3/4" - Black	12	61.22	1555	61.79	1569
K120620RPM	K12 1 21/32" x 62 3/4" - Black	12	62.08	1577	62.74	1594
K120640RPM	K12 1 21/32" x 64 3/4" - Black	12	64.07	1627	64.73	1644

PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K120650RPM	K12 1 21/32" x 65 5/8" - Black	12	64.97	1650	65.63	1667
K120655RPM	K12 1 21/32" x 66" - Black	12	65.5	1664	66	1676
K120660RPM	K12 1 21/32" x 66 5/8" - Black	12	65.99	1676	66.65	1693
K120665RPM	K12 1 21/32" x 67" - Black	12	66.5	1689	67	1702
K120670RPM	K12 1 21/32" x 67 5/8" - Black	12	66.98	1701	67.64	1718
K120675RPM	K12 1 21/32" x 68" - Black	12	67.5	1715	68	1727
K120680RPM	K12 1 21/32" x 68 1/2" - Black	12	68	1727	68.5	1740
K120702RPM	K12 1 21/32" x 70 3/4" - Black	12	70.23	1784	70.793	1798
K120815RPM	K12 1 21/32" x 82" - Black	12	81.46	2069	82.026	2083
K120842RPM	K12 1 21/32" x 84 3/4" - Black	12	84.23	2139	84.799	2154
K120864RPM	K12 1 21/32" x 86 7/8" - Black	12	86.36	2194	86.93	2208
K120878RPM	K12 1 21/32" x 88 3/8" - Black	12	87.82	2231	88.387	2245
K120891RPM	K12 1 21/32" x 89 5/8" - Black	12	89.12	2264	89.625	2278
K120903RPM	K12 1 21/32" x 90 7/8" - Black	12	90.31	2294	90.873	2308
K120924RPM	K12 1 21/32" x 93 1/8" - Black	12	92.5	2350	93.07	2364
K120931RPM	K12 1 21/32" x 93 3/4" - Black	12	93.19	2367	93.755	2381
K120964RPM	K12 1 21/32" x 97" - Black	12	96.41	2449	96.98	2463
K120979RPM	K12 1 21/32" x 98 1/8" - Black	12	97.54	2478	98.11	2492
K121039RPM	K12 1 21/32" x 104 1/2" - Black	12	103.94	2640	104.5	2654
K140234RPM	K14 1 15/16" x 24" - Black	14	23.4	594	24	610
K140580RPM	K14 1 15/16" x 58 5/8" - Black	14	58.09	1475	58.655	1490
K140618RPM	K14 1 15/16" x 62 3/8" - Black	14	61.83	1570	62.395	1585
K140627RPM	K14 1 15/16" x 63 3/8" - Black	14	62.76	1594	63.33	1609
K140662RPM	K14 1 15/16" x 66 3/4" - Black	14	66.19	1681	66.755	1696
K140682RPM	K14 1 15/16" x 68 3/4" - Black	14	68.18	1732	68.745	1746

For more information on any of these products, please contact your Gates Sales Representative.

© 2017 Gates Corporation. All rights reserved.
428-3291 REV 5/17



GATES.COM

Follow GatesRPM

Follow GatesAuto

