



POSILACE™ MECHANICAL BELT FASTENING SYSTEM

Pin fastening system allows for fast, tool-free, belt installations for lightweight to medium load applications

FEATURES

- Low profile for use with scrapers
- Unique, self-locking pin
 - Pin can be removed without damage to belt or pin
- Designed to reduce contamination risk through hinge loop breakage
 - In an overload situation, unlike plastic modular belting, the locking pin will fail first before the hinge loops break



PosiLace can be field welded to base belt using a Flexco® AMIGO™ press or can be factory prepped.


REQUIREMENTS

- Minimum pulley diameter - 6.27" (159 mm)
- Maximum belt width 42"

Max. Allowable Tension (lbs. per inch width)

	Standard	Cold Temp
PC20	26	26

	Single Track				Double Track	
	6" to 9"	>9" to 12"	>12" to 17"	>17" to 36"	>30" to 39"	>39" to 42"
CC40	155	179	206	223	471	498



GATES
 9 Northwestern Drive
 Salem, NH 03079
 Tel. +1 (603) 890-1515
 Tel. +1 (800) 394-4844
 Fax +1 (603) 890-1616
 Email: contact@gatesmectrol.com
GatesMectrol.com

© Copyright 2018 Gates Mectrol Incorporated.
 All rights reserved

GM PosiLace 8-2018